

## Specification Sheet

Part Number: PBM10M4



Push Mounts, when used with standard cable ties, provide a permanent bundling solution below a panel. The "button" style head is ideal for space constrained areas and is easily inserted through a pre-drilled hole.

Push-Button Cable Tie Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, White, 1000/pkg

**Article Number** 151-00231

**Type** PBM

**Color** White (WH)

**Quantity Per** bag

**Product Description** HellermannTyton push mounts are used with our standard cable ties and offer a permanent bundling solution for installation below or underneath a panel. Designed for simple installation by pushing the mount through a pre-drilled hole. The low profile "button" style head is suitable in space constrained areas.

**Short Description** Push-Button Cable Tie Mount, .25" Hole Dia, .12" Max Panel, .2" Max Tie Width, PA66, White, 1000/pkg

**Global Part Name** PBM-PA66-WH

**Width W (Imperial)** 0.26

**Width W (Metric)** 6.6

**Cable Ties** T18 - T50

**Height H (Imperial)** .40

**Height H (Metric)** 10.20

**Cable Tie Width Max (Imperial)** 0.2

**Cable Tie Width Max (Metric)** 5.0

**Panel Thickness Max (Imperial)** 0.12

**Panel Thickness Max (Metric)** 3.0

**Mounting Hole Diameter D (Imperial)** 0.25 - 0.29

**Mounting Hole Diameter D (Metric)** 6.25 - 6.55 mm

**Mounting Hole Diameter D Min (Imperial)** 0.25

**Mounting Hole Diameter D Max (Imperial)** 0.29

**Mounting Hole Diameter D Max (Metric)** 6.55

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V-2
<b>Operating Temperature</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Compliant</b>	Yes
<b>Certification/Specification</b>	UL
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity (Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988