Мацок Mallory Sonalert Products, Inc. Part #: JT028-RG-CS Revision: **Sales Outline Drawing** D Specifications: Stack Number: LED Color: RED GREEN Connection Wires: Red and Brown Green and Brown LED Current Draw: <50 mA <40 mA Rated Voltage: 24 VAC/DC Operating Voltage: 20-28 VAC/DC Total Max Current: <90mA -25° ~ +60°C Operating Temperature: Opaque White Lens Color: Material: ABS FR15U Mounting Method: Stainless Steel Pole 580 Weight Typical (g): NEMA 12: Approved Please contact factory. Options: **cUL** Recognized **ROHS Compliant** Dimensions: Inches (mm) PATENT NUMBER(S) D898600 10309594 3.8 [95.4]-GASKET -16.7 [423.2]-Ø0.57 [Ø14.6] for wires Ø0.20 [Ø5.2] 3 places #10 or 5mm screws for mounting 2.4 [61.8] 2.04 [51.9] T0:39 [3:3] 0.95 [24.3] 0.95 [24.3] 2.7 [68.3] MOUNTING DIAGRAM TOP VIEW LED OPERATION: CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.