

Specification Sheet

Part Number: FPB



Can be cut to length with scissors, eliminating waste and keeping stock to a minimum.

Available in 9 sizes, for thicknesses from .016" to .512", insuring proper fit.

Grommet, Panel Thickness 0.051"-0.083", PE, Natural, 82ft/pkg

Article Number 251-10209

Type G51PB

Color Natural (NA)

Quantity Per reel

Product Description HellermannTyton's Flexiform grommet is a unique, continuous wire protection product which fits easily in all shapes and sizes of holes without the aid of tools or adhesives. Flexiform grommet can be used on any type of material including wood, steel, aluminum, plexiglass, and glass.

Short Description Grommet, Panel Thickness 0.051"-0.083", PE, Natural, 82ft/pkg

Global Part Name G51PB-PE-NA

Length L (Imperial)	82.0
Variant	Open
Width W (Imperial)	0.181
Width W (Metric)	4.6
Height H (Imperial)	0.169
Height H (Metric)	4.3
Panel Thickness Min (Imperial)	0.051
Panel Thickness Max (Imperial)	0.083
Panel Thickness Min (Metric)	1.30
Panel Thickness Max (Metric)	2.10
Material	Polyethylene (PE)
Material Shortcut	PE
Flammability	UL 94 HB
Halogen Free	Yes

Operating Temperature -22°F to +176°F (-30°C to +80°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 82

Package Quantity (Metric) 25

Customs Number 3926909988