


Frames	Polyamide PA66 GF25 V-0
Sealing	TPE TPS



Properties

- Technology: Tool-free entry and connecting technology for machines and equipment
- Application: Insertion and sealing of pre-assembled cables with connectors into housings
- Variants of grommets: order as accessory from series F311-9xxx-zz, 7 small grommets for cables $\varnothing C = 3,0 - 16,0$ mm, 9 large grommets for cables $\varnothing C = 15,0 - 32,5$ mm, 1 small and 1 large grommet closed
- Mounting: mounting in wall thickness from 1,5 - 2,0mm, for walls with thickness larger 2,0 mm the KADL can be fixed with screws

Temperature range	-30 °C +100 °C
Protection grade	IP65
Test standard	UL 514B
UL / CSA-File	E140310




Features

● schwarz

Frame set without grommets

Description	Hole size	L	L1	H	H1	Grommet small	Grommet large	VPE	Part No.
KADL 1K/2G	125 x 35	153	63	32,3	8,9	1	2	1	F310-9035-01
KADL 5K	125 x 35	153	63	32,3	8,9	5	0	1	F310-9035-02
KADL 10K	125 x 57,5	153	85,5	32,3	8,9	10	0	1	F310-9057-01

Descri ption	Hole size	L	L1	H	H1	Grom met small	Grom met large	 VPE	Part No.
KADL 2K/4G	125 x 80	153	108	32,3	8,9	2	4	1	F310-9080-01
KADL 6K/2G	125 x 80	153	108	32,3	8,9	6	2	1	F310-9080-02
KADL 15K	125 x 80	153	108	32,3	8,9	15	0	1	F310-9080-03
KADL 11K/2G	125 x 102,5	153	130,5	32,3	8,9	11	2	1	F310-9102-01
KADL 20K	125 x 102,5	153	130,5	32,3	8,9	20	0	1	F310-9102-02
KADL 3K/6G	125 x 125	153	153	32,3	8,9	3	6	1	F310-9125-01
KADL 7K/4G	125 x 125	153	153	32,3	8,9	7	4	1	F310-9125-02
KADL 16K/2G	125 x 125	153	153	32,3	8,9	16	2	1	F310-9125-03
KADL 25K	125 x 125	153	153	32,3	8,9	25	0	1	F310-9125-04