


TECHNICAL DATA

Voltage	12.00 V
Performance	7.2Ah C20 to 1.75V/cell at 25°
Float Voltage	2.27V/cell at 20°C
Connection torque	na
Max Charge Current	1.80 A
Weight (Typical)	2.6 KG



ELECTRICAL PERFORMANCES

Constant Current Discharge Table [A] at 20°C

V / cell	5 min	10 min	15 min	30 min	45 min	1 h	2 h	3 h	4 h	5 h	6 h	8 h	10 h
1,60	23,0	18,3	14,9	8,62	6,02	4,64	2,54	1,84		1,25			0,71
1,65	22,5	17,9	14,5	8,50	5,91	4,57	2,51	1,82		1,25			0,70
1,67	22,0	17,4	14,2	8,38	5,85	4,50	2,48	1,80		1,24			0,70
1,70	21,5	17,0	13,8	8,27	5,78	4,43	2,44	1,78		1,23			0,69
1,75	20,8	16,2	13,2	8,05	5,61	4,30	2,38	1,73		1,19			0,68
1,80	19,8	15,4	12,6	7,80	5,48	4,18	2,34	1,69		1,17			0,67
1,85	18,9	14,7	12,0	7,49	5,28	4,04	2,26	1,64		1,12			0,65
1,90													

Constant Power Discharge Table [W/cell] at 25°C

V / cell	5 min	10 min	15 min	30 min	45 min	1 h	2 h	3 h	4 h	5 h	6 h	8 h	10 h
1,60	43,0	35,0	28,8	17,2	11,8	9,00	4,97	3,67		2,55			1,46
1,65	42,4	34,3	28,3	17,0	11,7	8,94	4,91	3,65		2,53			1,45
1,67	41,8	33,7	27,7	16,8	11,6	8,88	4,85	3,63		2,50			1,44
1,70	41,2	33,2	27,0	16,6	11,5	8,82	4,80	3,60		2,48			1,43
1,75	40,0	32,0	26,0	16,2	11,4	8,72	4,70	3,53		2,42			1,41
1,80	38,5	30,8	25,2	15,8	11,1	8,58	4,62	3,47		2,35			1,38
1,85	37,0	29,6	24,3	15,3	10,8	8,34	4,48	3,36		2,28			1,34
1,90													