


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00575	Connector, USB A 2.0 plug, molding style, 180°, nickel plated shell, white insulator	1	
2	50-00584	Connector, plug, USB micro B	1	
3	30-00099	Wire, 4C, 1PR + 2C, 28 AWG, UL2725, 30V, 80C, 3.6mm, shielded, VW-1, PVC, 79A, USB 2.0, white	1	
4	24-00210	Overmold, plug, USB A, slim design for aluminum shell	1	PVC, white
5	24-00218	Overmold, plug, USB micro and mini, slim design for aluminum shell	1	PVC, white
6	55-00106	USB A plug aluminum shell, 13x13.5x5.9 mm, silver	1	
7	55-00108	USB mini & micro aluminum shell, 13x9.6x5.8 mm, silver	1	



Wiring diagram		
50-00575	Wire Color	50-00584
1	Red	1
2	White	2
3	Green	3
4	Black	5
Shell	Drain & Shield	Shell

Notes:
Functionally equivalent components may be substituted

Revision:	Date:	Description:	Prepared:	Notes: RoHS compliant	TENSILITY tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com
A	1/16/2018	Initial release	Verified:		
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description: Cable, 1000 mm, 50-00575 USB A plug to 50-00584 USB B micro plug, 28 AWG, 30-00099 wire, white	Size: Part number: A 10-02351
					Scale: 1:1 Sheet 1 of 1

5

4

3

2

1