



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	COMBINED DWG OF MP-6ARJ45SBLK GRN/RED/BLU		20/AUG/2019	
A1	ADD LENGTH & UPDATE TOLERANCE:		5/SEP/2019	



Remark: Cable length 6 inches or shorter
Label in the middle of the cable.

PIN OUT: T568B	PIN OUT: T568B	COLOR
PLUG 1	PLUG 2	
PIN1	PIN1	WHITE/ORANGE
PIN2	PIN2	ORANGE
PIN3	PIN3	WHITE/GREEN
PIN4	PIN4	BLUE
PIN5	PIN5	WHITE/BLUE
PIN6	PIN6	GREEN
PIN7	PIN7	WHITE/BROWN
PIN8	PIN8	BROWN
Shielded	Shielded	DRAIN WIRE

CABLE COLOR:
BLACK, GREEN, RED, BLUE, GREY, WHITE, YELLOW




UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

DECIMALS	±.X	ANGLES	±X°
.XX	±.XX		
.XXX	±.XXX		

APPROVALS	DATE
LF	20/AUG/2019
BA	20/AUG/2019

Amphenol Cables on Demand
20 VALLEY ST. ENDCOTT, NY 13760

ASM CBL RJ45/RJ45 CAT.6A
FTP 4PR 26AWG(7*0.16)



DRWING	CHECKED	RES'P ENG	MFG ENG
LF	BA		

SIZE	DWG. NO.	REV.
A	MP-6ARJ45SXXX-XXX	A1

NOTES: UNLESS OTHERWISE SPECIFIED

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL CABLES ON DEMAND. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES IN PART OR WHOLE WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL CABLES ON DEMAND IS PROHIBITED.

REV.	DESCRIPTION	REVISIONS	DATE	APPROVED
A	COMBINED DWG OF MP-6ARJ45SBLK-GRN/RED-BLU GRY, WHT, YLW.		20/Aug/2019	
A1	ADD LENGTH & UPDATE TOLERANCE.		5/Sep/2019	

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SBLK-004IN	7084763	BLACK	4IN(102+20/-0mm)
MP-6ARJ45SBLK-006IN	7098098	BLACK	6IN(152+20/-0mm)
MP-6ARJ45SBLK-010	7078503	BLACK	10FT(3000+100/-0mm)
MP-6ARJ45SBLK-020	7075861	BLACK	20FT(6000+100/-0mm)
MP-6ARJ45SBLK-030		BLACK	30FT(9144+150/-0mm)

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SSGRN-000.5M		GREEN	0.5M(500+30/-0mm)
MP-6ARJ45SSGRN-001M	7347649	GREEN	1M(1000+50/-0mm)
MP-6ARJ45SSGRN-004	7347650	GREEN	4FT(1219+50/-0mm)
MP-6ARJ45SSGRN-005	7347651	GREEN	5FT(1524+50/-0mm)
MP-6ARJ45SSGRN-006	7361168	GREEN	6FT(1829+75/-0mm)
MP-6ARJ45SSGRN-007	7352842	GREEN	7FT(2134+75/-0mm)
MP-6ARJ45SSGRN-008	7361170	GREEN	8FT(2438+75/-0mm)
MP-6ARJ45SSGRN-010	7078507	GREEN	10FT(3000+100/-0mm)
MP-6ARJ45SSGRN-012	8201381	GREEN	12FT(3658+100/-0mm)
MP-6ARJ45SSGRN-015	8201383	GREEN	15FT(4572+100/-0mm)
MP-6ARJ45SSGRN-020	8201385	GREEN	20FT(6096+150/-0mm)

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SRED-001M	7321283	RED	1M(1000+30/-0mm)
MP-6ARJ45SRED-003		RED	3FT(914.4+30/-0mm)
MP-6ARJ45SRED-004	7347647	RED	4FT(1219+50/-0mm)
MP-6ARJ45SRED-005	7347648	RED	5FT(1524+50/-0mm)
MP-6ARJ45SRED-006	7361164	RED	6FT(1829+75/-0mm)
MP-6ARJ45SRED-007	7352841	RED	7FT(2134+75/-0mm)
MP-6ARJ45SRED-008	7361167	RED	8FT(2438+75/-0mm)
MP-6ARJ45SRED-010	7078505	RED	10FT(3000+100/-0mm)
MP-6ARJ45SRED-012	8201380	RED	12FT(3658+100/-0mm)
MP-6ARJ45SRED-015	8201382	RED	15FT(4572+100/-0mm)
MP-6ARJ45SRED-020	8201384	RED	20FT(6096+150/-0mm)
MP-6ARJ45SRED-030		RED	30FT(9144+150/-0mm)

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SBLU-000.5M		BLUE	0.5M(500+30/-0mm)
MP-6ARJ45SBLU-005		BLUE	5FT(1524+30mm)
MP-6ARJ45SBLU-007	7309910	BLUE	7FT(2134+50mm)
MP-6ARJ45SBLU-010	7078504	BLUE	10FT(3000+100/-0mm)
MP-6ARJ45SBLU-014	7337119	BLUE	14FT(4267+100/-0mm)
MP-6ARJ45SBLU-025	7340807	BLUE	25FT(7620+100mm)
MP-6ARJ45SBLU-050	7340808	BLUE	50FT(15240+200mm)
MP-6ARJ45SBLU-075	7340809	BLUE	75FT(22860+300mm)
MP-6ARJ45SBLU-100	7340810	BLUE	100FT(30480+300mm)
MP-6ARJ45SBLU-150	7340811	BLUE	150FT(45720+500mm)
MP-6ARJ45SBLU-200	7340812	BLUE	200FT(60960+1000mm)
MP-6ARJ45SBLU-250	7340813	BLUE	250FT(76200+12000mm)

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SGRY-010	7343698	GREY	10FT(3000+100/-0mm)
MP-6ARJ45SGRY-025	7340799	GREY	25FT(7620+100/-0mm)
MP-6ARJ45SGRY-050	7340800	GREY	50FT(15240+200mm)
MP-6ARJ45SGRY-075	7340801	GREY	75FT(22860+300mm)
MP-6ARJ45SGRY-100	7340802	GREY	100FT(30480+300mm)
MP-6ARJ45SGRY-150	7340803	GREY	150FT(45720+1000/-0mm)
MP-6ARJ45SGRY-200	7340804	GREY	200FT(60960+1000mm)
MP-6ARJ45SGRY-250	7340805	GREY	250FT(76200+2000mm)

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SWHT-005		WHITE	5FT(1524+30mm)
MP-6ARJ45SWHT-007		WHITE	7FT(2134+50mm)
MP-6ARJ45SWHT-010		WHITE	10FT(3000+100mm)

ACD P/N	Oracle P/N	COLOR	LENGTH
MP-6ARJ45SYLW-012	8200467	YELLOW	12FT(3658+75/-0mm)



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:

DECIMALS	±.X	ANGLES	±.X
X	±.XX		±.X
XX	±.XXX		±.XXX
XXX			

THIRD ANGLE PROJECTION

EAR NO.		DATE	
APPROVALS		DATE	
DRAWN	LF	20/Aug/2019	
CHECKED	BA	20/Aug/2019	
RESP ENG			
MFG ENG			

ASM CBL RJ45/RJ45 CAT.6A
FTP 4PR 26AWG(7*0.16)

MP-6ARJ45SXXX-XXX

NOTES: UNLESS OTHERWISE SPECIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[MP-6ARJ45SNNG-003](#) [MP-6ARJ45SNNG-001](#) [MP-6ARJ45SNNG-007](#) [MP-6ARJ45SNNG-020](#) [MP-6ARJ45SNNG-040](#) [MP-6ARJ45SNNG-010](#) [MP-6ARJ45SNNG-014](#) [MP-6ARJ45SNNG-030](#) [MP-6ARJ45SNNG-065](#) [MP-6ARJ45SNNG-050](#) [MP-6ARJ45SNNG-005](#) [MP-6ARJ45SNNG-025](#) [MP-6ARJ45SNNW-030](#) [MP-6ARJ45SNNW-010](#) [MP-6ARJ45SNNW-020](#) [MP-6ARJ45SNNW-065](#) [MP-6ARJ45SNNW-003](#) [MP-6ARJ45SNNW-007](#) [MP-6ARJ45SNNW-014](#) [MP-6ARJ45SNNW-001](#) [MP-6ARJ45SNNW-050](#) [MP-6ARJ45SNNW-025](#) [MP-6ARJ45SNNK-010](#) [MP-6ARJ45SNNK-030](#) [MP-6ARJ45SNNK-003](#) [MP-6ARJ45SNNK-005](#) [MP-6ARJ45SNNK-001](#) [MP-6ARJ45SNNK-020](#) [MP-6ARJ45SNNK-065](#) [MP-6ARJ45SNNK-014](#) [MP-6ARJ45SNNK-050](#) [MP-6ARJ45SNNK-007](#) [MP-6ARJ45SNNK-025](#) [MP-6ARJ45SNNR-025](#) [MP-6ARJ45SNNR-020](#) [MP-6ARJ45SNNR-014](#) [MP-6ARJ45SNNR-010](#) [MP-6ARJ45SNNR-005](#) [MP-6ARJ45SNNR-065](#) [MP-6ARJ45SNNR-007](#) [MP-6ARJ45SNNR-030](#) [MP-6ARJ45SNNR-003](#) [MP-6ARJ45SNNR-050](#) [MP-6ARJ45SNNR-001](#)