


M12 MALE 0° SHIELDED WIREABLE SCREW TERM.


8-pol. max.0.5mm² 6-8mm


[Link to Product](#)

Illustration



Male





Product may differ from Image

Form

Form 17341

Technical Data

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 2 A
Connection cross section	max. 0.5 mm ²
Sealing range (cable Ø)	6...8 mm
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Housing	Brass, nickel plated

General data

Temperature range -25...+85 °C

Commercial data

country of origin	DE
customs tariff number	85369010
EAN	4048879195317
eClass	27279218
minimum order quantity	1