


Spherical roller bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
55	120	29	156	166	18,6	5600	7500	1,70	21311 E *



Calculation factors
 e 0,25
 Y_1 2,7
 Y_2 4
 Y_0 2,5