




Cable Ties Polyamide 6.6 standard T30R



T-Series in PA66 black, Article number: 111-03011

- Available in a wide range of material and sizes
- Made from 100% high quality plastic, allows for good recycling
- Inside serration for a strong hold onto bundles
- Easy application either manually or with a processing tool
- Simply to insert due to bent tail

These cable ties are used for routing, bundling and securing of cables, pipes and hoses.



Base Data

Application Tool	MK3SP, MK3PNSP2, MK7P, MK7, MK20
Colour	Black (BK)
Fixation Method (FF)	None
Identification Plate Position	none
Product Family	T-Series in PA66 black
Product Group	Cable Ties Polyamide 6.6 standard
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Type	T30R.NB3P
Variant	Inside Serrated

Product Dimensions

Bundle Ø max.	35.0 mm
Bundle Ø max. (imperial)	1.38 "
Bundle Ø min.	1.5 mm
Bundle Ø min. (imperial)	0.06 "
Length (L)	150 mm
Length (L) (imperial)	5.9 "
Min. Tensile Strength (lbs)	30 lbs
Min.Tensile Strength (N)	135 N
Width (W)	3.5 mm
Width (W) (imperial)	0.14 "

Logistic and Packaging

EAN code	5022660018770
Pack Cont.	100
Quantity per	Bag
Weight	0.7 kg

Material and Specifications

Flammability	UL94 V2
Material	PA66
Material	Polyamide 6.6 (PA66)
Operating Temperature	-40 °C to +85 °C, (+105 °C, 500 h)
Specification	UL ZODZ2.E64963, DIN 30015955