

Product Information



1475PAO050P30-11

EAN 4031582338485

Swivel castor with wheel brake, housing made of pressed steel, bright zinc plated, blue passivated, double ball bearing swivel head, bolt hole. Wheel centre made of Polypropylene, Tread: Polyurethane, plain bearing

Technical Data	
Wheel diameter	50 mm
Width of Tread	19 mm
Centre hole	11 mm
Offset	25 mm
Swivel Interference	128 mm
Overall height	70 mm
Temperature	- 20 / + 60 °C
Standard	EN 12530
Weight	0.16 kg
Swivel Radius	64 mm
Hardness of tread	Shore D 40
Load capacity	40 kg
Load capacity (static)	80 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



1475PAO050P30-11

EAN 4031582338485

