

Product Information



UAR100x32-Ø12 HL44,4 red

EAN 4031582323108

Wheel centre made of Polyamide, Tread:
Polyurethane, roller bearing

Technical Data

Wheel diameter	100 mm
Width of Tread	32 mm
Axle Hole-Ø	12 mm
Hub length	44.4 mm
Temperature	- 40 / + 80 °C
Standard	EN 12532
Weight	0.208 kg
Hardness of tread	Shore D 40
Load capacity	150 kg
Load capacity (static)	300 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

