

JKL PART NUMBER	-A- LENGTH	LCD HIGH OUTPUT WHITE RGB COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms) TYP.	OPERATING LAMP VOLTAGE VL (Vrms) TYP.	OPERATING LAMP CURRENT IL (mArms)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS) MINIMUM
BF2698-20B	98±2.0		690 @ 0°C	275		30,000 TYP.	20,000.
BF26188-20B	188±3.0		1115 @ 0°C	405			
BF26214-20B	214±2.0	5,400°k	1150 @ 0°C	460			
BF26171-20B	171±3.0	x = .336 y = .353	957@25°C	390@25°C	5 ± 1		
BF26285-20B	285±1.5		1525 @ 0°C	610			
BF26318-20B	318±1.5		1710 @ 0°C	685			
BF26360-20B	360±1.5		1940 @ 0°C	775			

NOTES:

* RATED LIFE IS DEFINED AS THE POINT WHICH INTENSITY BECOMES 50% OF THE INITIAL RATING.

RATING AT 25°C UNLESS OTHERWISE SPECIFIED.

			METRIC DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS		JKL COMPONENTS CORPORATION						
F	ADD PART NO. BF26171-20B 1/20/1 RATED LIFE HRS MINIMUM HEADING & 20,000 8/5/09		 (OTHERWISE SPECIFIED 1 PL +/-		TITLE	MIN	IATURE COLI			
ᆫ	,		<u> </u>		REF.		IVIIIN	IATONE COLI	DCATHODE		
D	WIRE LENGTH TOLERANCE CHANGE 3/25/08 BF26285-20B LENGTH TOLERANCE CHANGE 2/3/06		THIRD ANGLE			FLUORESCENT LAMP					
С			PROJECTION	ANGLE +/- REF.							
В	ADD PART BF2698-20B	2/1/04	DRAWN BY	APPV'D BY	DATE	SIZE	FSCM NO.	DRAWING			
Α	ELECTRICAL CHNG. & ADD BF26318 & BF26360		L. WENGSTROM	L.R.	1/20/10	Α	55335	5 NO. BF26-20B			
	RELEASED TO CAD MULTI LIST 8/					SCALE		RELEASED	REVISION	I DEV	SHEET
REV.			- CAD DRAWING -		-	SCALE	NONE	DATE 8/14/03	DATE 1/20/1	NO. F	14 4 1
NO.	NO. NUMBER		MANUAL REVISIONS NOT PERMITTED			NONE	0/14/03	1/20/1	<u>'</u>	I OF I	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

JKL Components:

BF26214-20B BF26360-20B BF2698-20B