
# BCC M435-0000-2A-000-51X575-000

**Order Code: BCC06EY** 









Basi		

Approval/Conformity CE cURus EAC WEEE

### **Electrical connection**

Cable diameter D 6...8 mm Connection M12x1-Male, Straight, 5-pin, Acoded Number of connectable contacts Can be fabricated System

## **Electrical data**

Operating voltage Ub 125 VDC / 125 VAC Rated current (40 °C) 4.0 A

## **Environmental conditions**

Ambient temperature -40...85 °C IP rating IP67

#### Material

Subject to change without notice: PV159465

Material contact carrier PA Material contacts Brass Material cover nut Die-cast zinc Material grip PA

## Mechanical data

Connection cross-section 0.14...0.75 mm<sup>2</sup> Tightening torque pigtail 0.6 Nm Type of wire mounting Screw terminals

### Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

# **Connector Drawings**



PIN 1-5 usable