

CentralTM Semiconductor Corp.

145 Adams Avenue, Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824

Manufacturers of World Class Discrete Semiconductors

2N5770

NPN SILICON RF TRANSISTOR

JEDEC TO-92 CASE (EBC)

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N5770 type is a NPN Silicon Epitaxial Planar Transistors designed for high frequency amplifier and oscillator applications.

MAXIMUM RATINGS (T_A = 25°C)

	SYMBOL		UNITS
Collector-Base Voltage	V _{CB0}	30	V
Collector-Emitter Voltage	V _{CEO}	15	V
Emitter-Base Voltage	V _{EBO}	3.0	V
Collector Current	I _C	50	mA
Power Dissipation	P _D	625	mW
Operating and Storage			
Junction Temperature	T _J , T _{stg}	-65 to +150	°C
Thermal Resistance	θ _{JA}	200	°C/W

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	MAX	UNITS
I _{CBO}	V _{CB} = 15V		10	nA
I _{CBO}	V _{CB} = 15V, T _A = 150°C		1.0	μA
BV _{CB0}	I _C = 1.0μA	30		V
BV _{CEO}	I _C = 3.0mA	15		V
BV _{EBO}	I _E = 10μA	3.0		V
V _{CE(SAT)}	I _C = 10mA, I _B = 1.0mA		0.4	V
V _{BE(SAT)}	I _C = 10mA, I _B = 1.0mA		1.0	V
h _{FE}	V _{CE} = 1.0V, I _C = 3.0mA	20		
h _{FE}	V _{CE} = 1.0V, I _C = 8.0mA	50	200	
f _T	V _{CE} = 10V, I _C = 8.0mA, f = 100MHz	900		MHz
C _{ob}	V _{CB} = 10V, I _E = 0, f = 1.0MHz		1.7	pF
C _{ib}	V _{EB} = 0.5V, I _C = 0, f = 1.0MHz		2.0	pF
G _{pe}	V _{CB} = 12V, I _C = 6.0mA, f = 200MHz	15		dB
P _O	V _{CB} = 15V, I _C = 8.0mA, f = 500MHz	30		mW
η	V _{CB} = 15V, I _C = 8.0mA, f = 500MHz	25		%
NF	V _{CE} = 6.0V, I _C = 1.0mA, R _G = 400Ω, f = 60MHz		6.0	dB

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms