
THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION						
REV.	DESCRIPTION	DATE	APPROVED			
В	Updated Tolerance	05-08-19	LY			



NOTES:

1. CABLE: UL2725

28AWG*1PR+28AWG*2C+AEB(AL) 65% OUTER JACKET: WHITE, OD: 4.0 ± 0.2mm

2. CONNECTOR: USB A TYPE MALE INSULATOR: WHITE PBT

PIN G/F

NICKEL PLATED SHELL

3. CONNECTOR: MICRO USB B TYPE MALE

INSULATOR: BLACK

PIN G/F

NICKEL PLATED SHELL

- 4. PVC MOLDED: 45P WHITE
- 5. ELECTRICAL TEST:
 - <1>.100% OPEN SHORT & MISS WIRE TEST
 - <2>.INSULATION RESISTANCE: DC300V 10M ohm MIN.
 - <3>. CONDUCTOR RESISTANCE: 2 ohm MAX.

CONNECTION

CN1	CN2
1 RED	1
2 WHITE GREEN	$\times \frac{2}{3}$
4BLACK	 5
SHELL-BRAID&DRAIN	— SHELL

CONTROLLED

Dim range (mm)	Tango 17-		tek Electron WCI DIVISIO 25010-03	ics Corp. N
0-1	0.15	Description: USB 4P(A)/M - MICRO USB 5P(B)/M		
1-6	0.20			
6-18	0.30	DEO# 2505D	LINIT	DEV D
18-50	0.50	RFQ# 2505D	UNIT: mm	REV. B
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	R. Nuti	06-13-13	LY / 06-13-13
250-500	1.20	06-13-13	00-13-13	217 00 13-13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Qualtek: 3025010-03