

**KB224 - Wire Wrapping Bit, 22-24 AWG - Data Sheet**

3 inch Wire Wrapping Bit. Fully compatible with any make or model wire wrapping tool. Gauge Size: 22-24 AWG. Wrap Type: Regular. Minimum Terminal Diagonal Inches: 0.054. Max Terminal Diagonal Inches: 0.073. Terminal Hole Depth Inches: 0.807. Effective Radius Inches: 0.111. Terminal Hole Diameter Inches: 0.075. Compatible Sleeve Part #: P2224.



Specifications	
Wrap Function	Wrap
Wrap Type	Regular
Wire Gauge	22-24 AWG (0.65-0.50 mm)
Maximum Terminal Diagonal	0.073" (1.85 mm)
Minimum Terminal Diagonal	0.054" (1.37 mm)
Terminal Hole Depth	0.807" (20.05 mm)
Terminal Hole Dia.	0.075" (1.9 mm)
Effective Radius	0.111" (2.82mm)
Wrap Post Size	0.045" (1.14 mm)
Sleeve Part No.	P2224 and P2224INS (Sold Separately)
Length	3" (76.2mm)
Weight	0.055 lbs
UPC No.	811490010550

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Tools:](#)

[KB224](#)