

Tact Switch

Q-2752


TYPE: **KS01A**




SPECIFICATIONS

Contact Type	SPST
Rating	DC 35V, 10mA
Contacts Resistance	30mΩ Max
Insulation Resistance	100MΩ Min
Minimum Load	DC 100V
Dielectric Strengths	AC 250V / 1 minute
Life Test	100 000 Cycles Min
Operating temperature range	-20°C to +60°C
Operating Force	V: 130 ± 50gf M: 250 ± 50gf

Outline Drawing





Mounting



Button Color

R	Red
Y	Yellow
G	Green
B	Blue
W	White
BK	Black

Circuitry



107023, Москва, ул. Буженинова, д. 16
 телефон: (495) 963-6120
 факс: (495) 963-4994
 e-mail: quartz1@quartz1.ru

111123, Москва, шоссе Энтузиастов, д31
 телефон/факс: (495) 788-8899 *многоканальный*
 e-mail: mqz@quartz1.ru