

Coaxial Cable Connector 11_TNC-50-7-2/133_N

Description

Straight cable plug

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 11 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | soldered |
| Outer contact | clamped |
| Weight | 0.0397 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|-----------------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Brass | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Coupling nut | Brass | SUCOPLATE (R) Plating |
| Gasket | VMQ (Silicone rubber) | |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00008068 |
| Catalogue drawing | DOU-00008070 |
| Assembly instruction | DOC-0000179854 |

Ordering Information

| | |
|----------------|----------------------|
| Single package | 11_TNC-50-7-2/133_NE |
|----------------|----------------------|

Additional Information

| | |
|-----------------|---------------------------------|
| Suitable cables | RG_213_/U, RG_214_/U, RG_393_/U |
|-----------------|---------------------------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_TNC-50-7-2/133_NE](#)