



# suction cup VASB-125-3/8-PUR-B

Part number: 1396067

FESTO



## Data sheet

Feature	Value
Suction cup height compensator	25 mm
Nominal size	7 mm
suction cup diameter	125 mm
suction cup volume	307 cm <sup>3</sup>
Effective suction diameter	101.8 mm
Position of connection	on top
Assembly position	Any
Suction cup shape	Round, bellows 1.5 conv
Operating pressure	-0.95 ... 0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-20 ... 60 °C
Retention force at nominal operating pressure	570 N
Product weight	294 g
Mounting type	Via vacuum port
Vacuum connection	G3/8
Colour	blue
Shore hardness	60 +/- 5
Material of threaded plug	Zinc die-casting
Materials note	Conforms to RoHS
Material suction cup	PUR