


SERIES

**1330R
1330**



Unshielded Surface Mount Inductors



Physical Parameters

	Inches	Millimeters
A	0.300 to 0.325	7.62 to 8.26
B	0.105 to 0.125	2.67 to 3.18
C	0.125 to 0.145	3.18 to 3.68
D	0.020 Min.	0.508 Min.
E	0.040 to 0.060	1.02 to 1.52
F	0.190 (Ref. only)	4.83 (Ref. only)
G	0.070 (Ref. only)	1.78 (Ref. only)

Weight Max (Grams) 0.30

Operating Temperature Range

Phenolic: -55°C to +125°C
Iron and Ferrite: -55°C to +105°C

Current Rating at 90°C Ambient

Phenolic: 35°C Rise
Iron and Ferrite: 15°C Rise

Maximum Power Dissipation at 90°C Ambient

Phenolic: 0.210 W
Iron: 0.090 W
Ferrite: 0.073 W

Marking Delevan; dash number; date code (YYWWL).

Note: An R before the date code indicates a RoHS component.

Example: 1330-42K
DELEVAN
42
1818A

Packaging Tape & reel (16mm): 7" reel, 500 pieces max.; 13" reel, 2200 pieces max.

Made In the U.S.A.

DASH NUMBER*	INDUCTANCE (µH) ±10%	TEST FREQUENCY (MHz)	SRF MINIMUM (MHz)	DC RESISTANCE MAXIMUM (OHMS)	CURRENT RATING MAXIMUM (mA)
--------------	----------------------	----------------------	-------------------	------------------------------	-----------------------------

SERIES 1330 PHENOLIC CORE						
-94K	0.10	40	25.0	680.0	0.08	1380
-96K	0.12	40	25.0	640.0	0.09	1300
-00K	0.15	38	25.0	600.0	0.10	1230
-02K	0.18	35	25.0	550.0	0.12	1120
-04K	0.22	33	25.0	510.0	0.14	1040
-06K	0.27	33	25.0	430.0	0.16	975
-08K	0.33	30	25.0	410.0	0.22	830
-10K	0.39	30	25.0	365.0	0.30	710
-12K	0.47	30	25.0	330.0	0.35	660
-14K	0.56	30	25.0	300.0	0.50	550
-16K	0.68	28	25.0	275.0	0.60	500
-18K	0.82	28	25.0	250.0	0.85	420
-20K	1.00	25	25.0	230.0	1.00	390

SERIES 1330 IRON CORE						
-22K	1.20	25	7.9	150.0	0.18	620
-24K	1.50	28	7.9	140.0	0.22	560
-26K	1.80	30	7.9	125.0	0.30	480
-28K	2.20	30	7.9	115.0	0.40	415
-30K	2.70	37	7.9	100.0	0.55	355
-32K	3.30	45	7.9	90.0	0.85	285
-34K	3.90	45	7.9	80.0	1.00	263
-36K	4.70	45	7.9	75.0	1.20	239
-38K	5.60	50	7.9	65.0	1.80	195
-40K	6.80	50	7.9	60.0	2.00	185
-42K	8.20	55	7.9	55.0	2.70	160
-44K	10.00	55	7.9	50.0	3.30	144
-46K	12.0	45	2.5	40.0	2.70	160
-48K	15.0	45	2.5	35.0	2.80	157
-50K	18.0	45	2.5	30.0	3.10	149
-52K	22.0	45	2.5	25.0	3.30	144
-54K	27.0	45	2.5	20.0	3.50	140

SERIES 1330 FERRITE CORE						
-56K	33.0	35	2.5	24.0	3.40	130
-58K	39.0	35	2.5	22.0	3.60	125
-60K	47.0	35	2.5	20.0	4.50	110
-62K	56.0	35	2.5	18.0	5.70	100
-64K	68.0	35	2.5	15.0	6.70	92
-66K	82.0	35	2.5	14.0	7.30	88
-68K	100.0	35	2.5	13.0	8.00	84
-70K	120.0	30	0.79	12.0	13.00	66
-72K	150.0	30	0.79	11.0	15.00	61
-74K	180.0	30	0.79	10.0	17.00	57
-76K	220.0	30	0.79	9.0	21.00	52
-78K	270.0	30	0.79	8.0	25.00	47
-80K	330.0	30	0.79	7.0	28.00	45
-82K	390.0	30	0.79	6.5	35.00	40
-84K	470.0	30	0.79	6.0	42.00	36
-86K	560.0	30	0.79	5.0	46.00	35
-88K	680.0	30	0.79	4.2	60.00	30
-90K	820.0	30	0.79	3.8	65.00	29
-92K	1000.0	30	0.79	3.4	72.00	28

Optional Tolerances: J = 5% H = 3% G = 2% F = 1%
*Complete part # must include series # PLUS the dash #

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delevan:](#)

[1330-44K](#) [1330-34KTR](#) [1330R-44K](#) [1330R-88KTR](#) [1330-20KTR](#) [1330R-20KTR](#) [1330R-08G](#) [1330R-96G](#) [1330R-94KTR](#) [1330R-16KTR](#) [1330-02K](#) [1330-04K](#) [1330-06K](#) [1330-22K](#) [1330-60KTR](#) [1330-68K](#) [1330-96K](#) [1330R-00K](#) [1330R-02K](#) [1330R-04K](#) [1330R-06K](#) [1330R-08K](#) [1330R-10K](#) [1330R-12K](#) [1330R-14K](#) [1330R-16K](#) [1330R-18K](#) [1330R-20K](#) [1330R-94K](#) [1330R-96K](#) [1330-88K](#) [1330-88KTR](#) [1330-48K](#) [1330-40KTR](#) [1330R-04G](#) [1330-52K](#) [1330-94K](#) [1330-94J](#) [1330-94H](#) [1330-94G](#) [1330-94F](#) [1330-96J](#) [1330-96H](#) [1330-96G](#) [1330-96F](#) [1330-00K](#) [1330-00J](#) [1330-00H](#) [1330-00G](#) [1330-00F](#) [1330-02J](#) [1330-02H](#) [1330-02G](#) [1330-02F](#) [1330-04J](#) [1330-04H](#) [1330-04G](#) [1330-04F](#) [1330-06J](#) [1330-06H](#) [1330-06G](#) [1330-06F](#) [1330-08K](#) [1330-08J](#) [1330-08H](#) [1330-08G](#) [1330-08F](#) [1330-10K](#) [1330-10J](#) [1330-10H](#) [1330-10G](#) [1330-10F](#) [1330-12K](#) [1330-12J](#) [1330-12H](#) [1330-12G](#) [1330-12F](#) [1330-14K](#) [1330-14J](#) [1330-14H](#) [1330-14G](#) [1330-14F](#) [1330-16K](#) [1330-16J](#) [1330-16H](#) [1330-16G](#) [1330-16F](#) [1330-18K](#) [1330-18J](#) [1330-18H](#) [1330-18G](#) [1330-18F](#) [1330-20K](#) [1330-20J](#) [1330-20H](#) [1330-20G](#) [1330-20F](#) [1330-22J](#) [1330-22H](#) [1330-22G](#)