



**Product:** [83910](#)

Type T Thermocouple, 1 Pr #20 Sol, FEP Ins Blu, Red, Brn FEP Jkt, 300V CL3P 200C PLTC SUN RES

[Request Sample](#)

**Product Description**

Type T Thermocouple, 1 Pair 20AWG (Solid) OFHC+Constantan, FEP Insulation Blu, Red Color Code, Brown FEP Outer Jacket, CL3P 200C PLTC SUN RES

**Technical Specifications**

**Product Overview**

Suitable Applications:	Industrial Control, Raceways Cable trays and ducts, Digital Control, Instruments (4-20ma, 0-10v, ...), low voltage digital control (24v, ...), encoders, control circuits, distributed control
------------------------	--

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Pair(s)	1	20	Solid	Copper & Constantan

**Insulation**

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene	0.01 in (0.25 mm)	0.052 in (1.3 mm)	Blue and Red

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.012 in (0.30 mm)	0.128 in (3.25 mm)

**Electrical Characteristics**

**Electricals**

Element	Nom. Conductor DCR
Copper	10 Ohm/1000ft
Constantan	293 Ohm/1000ft (961 Ohm/km)

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**

**Temperature**

UL Temperature	Operating
200°C	-70°C To +200°C

**Bend Radius**

Stationary Min.	Installation Min.
1.28 in (32.5 mm)	1.28 in (32.5 mm)

Max. Pull Tension:	34 lbs
Bulk Cable Weight:	12 lbs/1000ft

**Standards and Compliance**

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum)
NEC / UL Compliance:	Article 725, CL3P, PLTC
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ISA MC 96.1-1982 Type T

## History

Update and Revision:	Revision Number: 0.442 Revision Date: 01-11-2022
----------------------	--

## Variants

Item #	Color	Putup Type	Length	UPC
83910 001100	Brown	Reel	100 ft	612825205883
83910 0011000	Brown	Reel	1,000 ft	612825205890

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[83910 001100](#) [83910 0011000](#)