

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Angle Grinder

GWS 12V-76 Professional



Satisfaction guaranteed - the most manageable small angle grinder

The most important data

Battery voltage	12 V
No-load speed	19.500 rpm
Grinding/cutting disc, diameter	76 mm

Part number: 0 601 9F2 000

[> More product information](#)

Technical Data

Performance data

No-load speed	19.500 rpm
Grinding spindle thread	M 5
Bore size, diameter	10,0 mm

Battery and power

Battery voltage	12 V
-----------------	------

Size and weight

Weight excl. battery	0.7 kg
----------------------	--------

Tools

Grinding/cutting disc, diameter	76 mm
---------------------------------	-------

Noise/vibration information

Surface grinding (roughing)

Vibration emission value ah	13,5 m/s ²
Uncertainty K	1,5 m/s ²

Noise

Sound pressure level	75 dB(A)
Sound power level	86 dB(A)
Uncertainty K	3 dB



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages

- Handy in every situation - extremely compact and ergonomic for fast disconnection on the construction site
- Fast work rate thanks to the high-performance EC motor
- Highly versatile for different materials
- The first 12 volt angle grinder
- Easy to swap discs thanks to the new spindle lock
- Easy adjustment of the protective cover without having to use tools

