

## SDS-Plus M2 Set GB - 5 pcs | SDS-Plus M2 drill bits - 2 cut / cassettes

Article: 4932352834



- Breaker Points. 3 offset aggressive power breakers. These produce a "Demolition" effect and create micro cracks in the drilled material. Up to 25% FASTER.
- Centering tip ensures immediate spot drilling with pin point accuracy. Prevents skidding on smooth surfaces.
- Enlarged rebar chamfers. Prevents side tip damage when hitting rebar. Reduces the risk of the drill bit jamming when hitting rebar.
- Tapered shoulder design. Thinner shoulder towards drill tip for less friction providing for greater speed. Ideal for cordless hammers identified from its tapered shoulder geometry.
- Reinforced flute. High volume flute geometry for optimum dust removal. Reinforced flute design (thicker core) gives: - Full power transfer to the tip. - Lower vibrations. - Exceptional break resistance, less breakages and best durability.
- Made in Germany.

	SDS-Plus M2 Set GB - 5 pcs
Supplied in	Plastic container
Article Number	4932352834
Contents	ø 5.5 x 110 mm and ø 5.5 / 6 / 7 / 8 x 160 mm.
Pack quantity	5