

SERIES


CM6350R CM6350

RoHS
Compliant
Traditional
First Quality


Surface Mount Common Mode Choke

DASH NUMBER
L1 or L2 INDUCTANCE
+35% / -23% (uH)
MAXIMUM (OHMS)
DC RESISTANCE
RATED RMS CURRENT
(AMPS) MAXIMUM
LEAKAGE INDUCTANCE
TYPICAL (uH)

Suppressors



SCHEMATIC



SERIES CM6350 FERRITE CORE				
-333	33	0.007	5.50	0.20
-473	47	0.008	5.00	0.30
-683	68	0.010	4.20	0.42
-104	100	0.014	3.30	0.55
-154	150	0.020	2.70	0.85
-224	220	0.027	2.20	1.20
-334	330	0.040	1.80	1.80
-474	470	0.060	1.50	1.60
-684	680	0.090	1.20	2.10
-105	1000	0.130	0.90	2.80
-155	1500	0.190	0.75	4.20
-225	2200	0.300	0.60	6.00
-335	3300	0.550	0.40	9.00
-475	4700	1.050	0.25	13.00

*Complete part # must include series # PLUS the dash #

Mechanical Configuration A flat top surface mount case with excellent coplanarity of terminals.

Physical Parameters

	Inches	Millimeters
A	0.285 ± 0.010	7.24 ± 0.25
B	0.360 ± 0.010	9.14 ± 0.25
C	0.060 ± 0.010	1.52 ± 0.25
D	0.350 ± 0.010	8.90 ± 0.25
E	0.200 ± 0.010	5.08 ± 0.25
F	0.025 ± 0.010	0.64 ± 0.25
G	0.040 (Ref. only)	1.02 (Ref. only)

Electrical Configuration

- 1) Inductance and DCR in table is for either L1 or L2.
- 2) Leakage Inductance tested at L1 with L2 shorted or at L2 with L1 shorted.
- 3) Windings balanced within 2%
- 4) Inductance tested @ 10 kHz

Operating Temperature Range -55°C to +105°C

Electrical Characteristics Measured at +25°C


Rated RMS Current Based upon 40°C temperature rise from 25°C ambient

Maximum Power Dissipation at 25°C 0.400 Watts

Inductance Tolerance Units are supplied to the tolerance indicated in the tables @ 10 kHz

Dielectric Withstanding Voltage

500 V RMS, 60Hz



Marking DELEVAN; CM6350, inductance with units. Note: An R after CM6350 indicates a RoHS component. A white dot indicates the location of pin 1.

Example: CM6350-333
DELEVAN
CM6350
33 uH

Packaging Tape & reel (24mm):
13" reel, 600 pieces max.; 7" reel not available
Bulk option available

Weight (Grams) 1.0 (Ref.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delevan:](#)

[CM6350-334](#) [CM6350-473](#) [CM6350-474](#) [CM6350-475](#) [CM6350-224](#) [CM6350-333](#) [CM6350-683](#) [CM6350-104](#)
[CM6350-154](#) [CM6350-684](#) [CM6350-105](#) [CM6350-155](#) [CM6350-225](#) [CM6350-335](#) [CM6350R-333](#) [CM6350R-473](#)
[CM6350R-683](#) [CM6350R-104](#) [CM6350R-154](#) [CM6350R-224](#) [CM6350R-334](#) [CM6350R-474](#) [CM6350R-684](#)
[CM6350R-105](#) [CM6350R-155](#) [CM6350R-225](#) [CM6350R-335](#) [CM6350R-475](#) [CM6350R-105 B100](#) [CM6350R-683-](#)
[REEL](#)