



# 567.3287-R INTERLOCKED SOCKET + RCD

32A 3P+N+E 6h 346-415V 50Hz 60Hz  
136X390MM Screw terminals With mechanical interlock

Product Approvals

| TECHDATA                |                          | STANDARDS AND LAWS                |   |
|-------------------------|--------------------------|-----------------------------------|---|
| Product type            | INTERLOCKED SOCKET + RCD | EN 60309-1 (1999)                 | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements  |
| Commercial series       | ADVANCE 2 Series         | EN 60309-2 (1999)                 | [European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations |
| Synthetical description | INTERLOCKED SOCKET + RCD |                                   |   |
| Mounting version        | SURFACE MOUNTING         | DIRECTIVE LOW VOLTAGE 2014/35 /UE | [European Directives] Low Voltage Directive   |
| Rated current           | 32A                      |                                   |   |
| Poles                   | 3P+N+E                   |                                   |   |
| Hour position           | 6h                       |                                   |   |
| Rated voltage (range)   | 250-400V                 |                                   |   |
| Rated voltage           | 346-415V                 |                                   |   |
| Working frequency       | 50Hz                     |                                   |   |
| Working frequency       | 60Hz                     |                                   |   |
| Colour                  | RED                      |                                   |   |
| Material                | THERMOPLASTIC            |                                   |   |
| Protection degree       | Splash proof             |                                   |   |
| Protection degree IP    | IP44                     |                                   |   |
| Protection degree IK    | IK07                     |                                   |   |
| Terminals               | Screw terminals          |                                   |   |
| Contact material        | CuZn (brass)             |                                   |   |

|             |                           |
|-------------|---------------------------|
| Flange      | 136X390MM                 |
| Cable entry | DRILLING POINT MARK       |
| Options     | With mechanical interlock |
| Notes       | WITH DIN RAIL (6 MODULES) |
| Padlock     | ø5mm                      |