


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	50-00024	Connector, dc plug, 5.5x2.1xL23 mm, molding style, spring contacts	1	
2	30-00003	Wire, 2C BC, 24 AWG, UL2468, 300V, 80C, 3.6 mm, VW-1, PVC	1	
3	24-00003	Overmold, PVC, black	1	



Wiring diagram	
50-00024	Wire Color
Center	Black with stripe
Sleeve	Black

Notes:
Functionally equivalent components may be substituted
Cable rated for 48 V, 6 A

Revision:	Date:	Description:	Prepared:	Notes:
A	6/28/2012	Initial release	RoHS compliant	Function test: no open, no short circuit, no intermittent
			Verified:	Description: Cable, 1830 mm, 5.5x2.1x12 mm 50-00024 dc plug to stripped tinned, 24 AWG, 30-00003 wire
			Dimensions are in millimeters.	
			Tolerances:	
			X: ± 0.5 mm	
			XX: ± 0.3 mm	
			XXX: ± 0.05 mm	

TENSILITY

tel 1.541.323.3228 800 877.670.7118
fax 1.541.323.4202 web tensility.com

Size: Part number:
A 10-01062

Scale: 1:2



Sheet 1 of 1