




7985

7985

NON-RETURN VALVE, SUPPLY FLOW, BSP TAPER

| | | | |
|--------------------------|---------------------------|-------------------|-----------------|
| maximum working pressure | bar | MPa | psi |
| | 10 | 1,0 | 145 |
| working temperature | °C (Celsius) | F (Fahrenheit) | K (Kelvin) |
| | From 0 to 70 | From 32 to 158 | From 273 to 343 |
| shut-off valve | nitrile | | |
| body | engineering grade polymer | | |
| sub-base | nickel-plated brass | | |
| 'O'-rings | nitrile | | |
| gripping ring | stainless steel | | |



7985
 NON-RETURN VALVE, SUPPLY FLOW, BSP
 TAPER
for metric tubing

7985

| Part No | ØD (mm) | C | F (mm) | H (mm) | ⚖️ (kg) |
|----------------|--------------------|----------|-------------------|-------------------|----------------|
| 7985 04 10 | 4 | R1/8 | 16,0 | 28,5 | 0,016 |
| 7985 06 10 | 6 | R1/8 | 16,0 | 30,5 | 0,016 |
| 7985 06 13 | 6 | R1/4 | 16,0 | 30,5 | 0,021 |
| 7985 08 10 | 8 | R1/8 | 19,0 | 36,0 | 0,022 |
| 7985 08 13 | 8 | R1/4 | 19,0 | 36,0 | 0,020 |