

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [50420-8000](#)
Status: **Active**
Description: OBD-II Crimp Terminal, Female, 50420, 4.00mm Pitch

Documents:

[Drawing \(PDF\)](#) [Application Specification AS-51115-001 \(PDF\)](#)
[Product Specification PS-51115-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	50420
Application	Power
Crimp Quality Equipment	Yes
Product Name	OBD-II
UPC	800754370233

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	173.000/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.60-1.40mm
Wire Size AWG	20, 22
Wire Size mm ²	0.50-0.30

Material Info

Reference - Drawing Numbers

Application Specification	AS-51115-001
Product Specification	PS-51115-001
Sales Drawing	SD-50420-8*00




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

50420Series

Use With

51115 , 51116

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for OBD II 4.00mm Wire-to- Wire Crimp Terminal, 0.30-0.85mm ² and 18-22 AWG	0639009700
Hand Crimp Tool	0638119500
Extraction Tool	0011030043

Japan

Description	Product #

Applicator for M21 1A 0573263000
Bench Press, 18-22
AWG Wire

This document was generated on 03/04/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION