



www.i-t.su
info@i-t.su

тел: (495) 739-09-95, 739-09-96

ИНТЕРТЕКС
electronics

Импульсные стабилизаторы

Код:	Ток [A]	Напряжение [B]	Корпус
LM2574HVN-5	0,5	5	DIP8
LM2574M-5.0	0,5	5	SO14L
LM2574N-3.3	0,5	3,3	DIP8
LM2574N-5	0,5	5	DIP8
LM2574N-ADJ	0,5	1,23-27	DIP8
LM2594HVM-ADJ	0,5	4,75-57	SO8
LM2594M-5.0	0,5	5	SO8
LM2597M-5.0	0,5	5	SO8
LM2671M-5.0	0,5	5	SO8
LM2674M-ADJ	0,5	8-37	SO8
LM2674N-5.0	0,5	5	DIP8
TL497ACN	0,5	5-12	DIP14
LTC1174CS8SMD	0,6	13,5	SO8
LTC1174HVCN8-5	0,6	5	DIP8
LT1776CS8-SMD	0,7	7,4-40 Vin	SO8
LM2575HVT-12	1,0	12	TO220-5
LM2575HVT-15	1,0	15	TO220-5
LM2575HVT-5	1,0	5	TO220-5
LM2575HVT-ADJ	1,0	1,23-57	TO220
LM2575N-5	1,0	5	DIP16
LM2575S-5.0	1,0	5	TO263
LM2575T-12	1,0	12	TO220
LM2575T-15	1,0	15	TO220-5
LM2575T-3.3	1,0	3,3	TO220-5
LM2575T-5	1,0	5	TO220
LM2575T-ADJ	1,0	1,23-37	TO2205
LM2595T-5.0	1,0	5	TO220
LM2675M-ADJ	1,0	8-37	SO8
LM2825N-ADJ	1,0	1,23-8	DIP24
LT1082CN8	1,0	3-75 Vin	DIP8
LT1082IN8	1,0	3-75 Vin	DIP8
LT1533CS	1,0	2,7-23 Vin	SO16
LT1176CN8	1,2	3,5-38 Vin	DIP8
LT1072CN8	1,25	1,25-70	DIP8
LT1072CT	1,25	3-60 Vin	TO220-5
LT1172CN8	1,25	3-60 Vin	DIP8
LT1172CT	1,25	3-60 Vin	TO220-5
L4962A-ST	1,5	5,1-40	DIP16
LT1373CN8	1,5	2,7-30 Vin	DIP8
LT1376CS8-5	1,5	5-25 Vin	SO8
LT1376CS8-SMD	1,5	5-25 Vin	SO8
LT1956EGN	1,5	5,5-60 Vin	SSOP16
MC34063AP1	1,5	1,25-35	DIP8
UA78S40	1,5	1,25-35	DIP16
L4972A	2,0	5,1-40	DIP20
LT1076CQ	2,0	8-45 Vin	D2PAK-5
LT1076CT	2,0	2,5-40	ZIP5
LT1076HVCT-5	2,0	5	TO220-5
L4960	2,5	5,1-40	ZIP7
LT1171CQ	2,5	3-60 Vin	DD-5
LT1171CT	2,5	3-60 Vin	TO220-5
LT1076CT-5	2,6	8-45 Vin	TO220-5
LT1076HVCT	2,6	8-64 Vin	TO220-5
LM2576HVT-12	3,0	12	TO220-5
LM2576HVT-15	3,0	15	TO220-5
LM2576HVT-3.3	3,0	3,3	TO220-5
LM2576HVT-5	3,0	5	TO220-5
LM2576HVT-ADJ	3,0	1,23-37	TO220
LM2576S-3.3	3,0	3,3	TO263
LM2576S-5	3,0	5	TO263
LM2576T-12	3,0	12	TO220
LM2576T-15	3,0	15	TO220-5
LM2576T-5	3,0	5	TO220
LM2576T-ADJ	3,0	1,3-37	TO220
LM2577T-ADJ	3,0	0-60	TO220
LM2585T-ADJ	3,0	1,23-37	TO2205
LM2596T-ADJ	3,0	4,75-37	TO2205
L4974A	3,5	5,1-40	DIP20
L296	4,0	5,1-40	ZIP15
L4964	4,0	5,1-40	ZIP15
L4975A	5,0	1-40	MULTIWATT
LM2678S-ADJ	5,0	8-37	TO263
LT1070CT	5,0	1,3-35	ZIP5
LT1070HVCT	5,0	3-60 Vin	TO220-5
LT1071CT	5,0	60	ZIP5
LT1074CT	5,0	2,5-40	ZIP5
LT1074CT7	5,0	8-45 Vin	TO220-7
LT1074HVCT	5,0	8-64 Vin	TO220-5
LT1170HVCT	5,0	3-60 Vin	TO220-5
LT1270CT	8,0	3,5-30 Vin	TO220-5
LTC1149CN		до 60 Vin	DIP16
LTC1149CS-SMD		до 60 Vin	SO16