


Sales Outline DrawingRevision **D****May not be suitable for all medical and aerospace applications.****Specifications: Contact Mallory Sonalert to discuss your application.**

| | |
|----------------------------------|---|
| Oscillation Frequency (Hz) | 3000 ± 500 |
| Operating Voltage (Vdc) | 3.0 ~ 24 |
| Rated Voltage (Vdc) | 12 |
| Current Consumption (mA/max) | 18 at Rated Voltage |
| Sound Pressure Level (dB/min) | 85 at 30cm at Rated voltage |
| Tone/Pulse Rate (Hz) | Slow Pulse 1.2 ±20% |
| Operating Temperature (°C) | -20 ~ +90 |
| Storage Temperature (°C) | -30 ~ +100 |
| Housing | ABS 777D UL94HB plastic resin (Color: Black) |
| Lead Pins | Tin Plated Brass |
| Weight (Grams) | 5.0 |
| Condition by wave soldering (°C) | 260 ±5 / within 5 sec |
| Condition by hand soldering (°C) | 350 ±20 / within 5 sec |
| Options | For other options contact factory |

Dimensions: (units: mm)**ROHS Compliant**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PL-21A31PQ](#)