

2776.0

HZL/1,0-D RD



Wire-end ferrules, Max. wire cross-section: 1 mm<sup>2</sup>, Length: 15 mm, Length of copper pipe: 8 mm, Colour: Red

## Business data

Packaging unit	500
Quantity unit	PC
Weight per piece (not including packaging)	0.14 g
Weight per piece (including packaging)	0.15 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules

2776.0

HZL/1,0-D RD

---

## Technical data

---

### Dimensions

---

Length	15 mm
Length of copper pipe	8 mm
Width of plastic collar	3.2 mm
Height of plastic collar	5.8 mm
Diameter of copper pipe	2 mm
Wall thickness of copper pipe	0.15 mm
Wall thickness of plastic collar	0.3 mm

### Connection data

---

Wire cross-section, max.	1 mm <sup>2</sup>
Wire cross-section AWG, max.	17
Stripping length	12 mm
2-wire plastic collar	✓

### Materials

---

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Plastic collar	Polypropylene homopolymer
Working temperature, min.	-5 °C
Working temperature, max.	105 °C

### Further technical data

---

Insulation available	✓
----------------------	---

### Print

---

Colour	Red
--------	-----

### Environmental Product Compliance

---

REACH Conform	yes
REACH Reference date	2021-01-09, 2021-07-08
REACH Candidate Substance Note	No
RoHS Conform	yes

# Data sheet

2776.0

HZL/1,0-D RD



---

## Approvals

---

### Standards and regulations

---

DIN 46228-4:1990	yes
------------------	-----

---

# Data sheet

2776.0

HZL/1,0-D RD



---

## Accessories

---