

2218.0

H 0,75/10



Wire-end ferrules, Max. wire cross-section: 0.75 mm², Length: 10 mm, Colour: natural

Business data

Packaging unit	1000
Quantity unit	PC
Weight per piece (not including packaging)	0.05 g
Weight per piece (including packaging)	0.06 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Ferrules

2218.0

H 0,75/10

Technical data

Dimensions

Length	10 mm
Diameter of copper pipe	1.2 mm
Diameter of feed-in funnel	2.3 mm
Wall thickness of copper pipe	0.15 mm

Connection data

Wire cross-section, max.	0.75 mm ²
Wire cross-section AWG, max.	18
Stripping length	10 mm

Materials

Copper pipe	Copper alloy
Surface	Galvanically tin-plated, shiny
Working temperature, max.	120 °C

Print

Colour	Natural
--------	---------

Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2021-07-08
REACH Candidate Substance Note	No
RoHS Conform	yes

Data sheet



2218.0

H 0,75/10

Approvals

Standards and regulations

DIN 46228-1:1992	yes
------------------	-----

Data sheet

2218.0

H 0,75/10



Accessories
