

- Modern design
- Simple mounting

#### Technical specifications:

##### Housing:

ABS/PC-Blend

##### Cap:

Polycarbonate, transparent

##### Fixing:

Base, bracket or tube mounting\*

##### Socket:

B 15 d, BA 15 s

##### Terminal:

Screw free clamp mechanism for  
2 x 0.75 mm<sup>2</sup> to 2 x 1.5 mm<sup>2</sup>  
Outer diameter 7 - 11 mm  
Protection rating to VDE specifications

##### Duty cycle:

100 % max. 10 W

##### Bulb not included in assembly

(\* Base 975 840 90 must be ordered twice for base mounting – once as socket for beacon and once as base.)

- High protection rating IP 65 – suitable for indoor and outdoor use

#### Order specifications:

##### Order No.

826 □ 00 00 Signal beacon, 12 - 240 V ≅  
BA 15 d (available 04/98)  
826 □ 20 00 Signal beacon, 24 V ≅  
BA 15 s

▲  
1 = red    3 = yellow

Please state colour code.

#### Special parts:

975 826 01 Bracket for wall mounting  
975 845 10 Tube ø 25 mm, 100 mm long  
Aluminium anodized  
975 840 90 Base for tube  
(order double)

Bulb BA 15 d, 42 mm  
955 826 35 24 V, 10 Watt  
955 826 38 230 V, 10 Watt  
Bulb BA 15 s, 52 mm  
955 021 35 24 V, 21 Watt



**NEW**

