



DCF897N

18V XR Brushless 3/4" High Torque Wrench - Bare Unit

Selling Proposition

- Powerful fan cooled motor delivers up to 950Nm of torque and 2400 impacts per minute for heavy duty fastening applications
- Latest generation 18V BRUSHLESS XR Li-Ion High Torque Wrench
- 3 Speed and torque settings gives you the control to best suit your application
- 3/4" (19 mm) square drive with detent pin allows for more efficient torque delivery and excellent socket retention
- Up to 1625Nm of "breakaway" torque ensures removal of the tightest bolts
- Bright white LED with delay feature for improved visibility and flashlight functionality

Standard Equipment

- 18V XR Brushless 3/4" High Torque Wrench - Bare Unit

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max Torque	950 Nm
Power Input	
Power Output	
No Load Speed	
Impacts per Minute	2400 ipm
Max. Bolt Diameter	
Bit Holder	
Weight	2.6 kg