

Number of contacts

# 9-25



IP 67, turned solder cups, with rear plastic mounting plate

Identification	No. of contacts	Part No.	
		S4 <sup>1)</sup>	
Male connector metal shell with dimples	9 15 25	09 67 509 .	615
		09 67 515 .	615
		09 67 525 .	615
Please insert digit for flange thread			
4-40 UNC ▶	7		
M3 ▶	9		
Female connector metal shell	9 15 25	09 67 509 .	715
		09 67 515 .	715
		09 67 525 .	715
Please insert digit for flange thread			
4-40 UNC ▶	6		
M3 ▶	8		

D-Sub - W

<sup>1)</sup> S4: ≥ 0.76 µm Au (30 µinch)

Number of contacts

# 9-25



IP 67, turned solder cups, with rear plastic mounting plate


Identification

Drawing

Dimensions in mm


### Male connector

9 – 25 contacts



### Female connector

9 – 25 contacts



	a	b	c	d
9	40.0	25.00	16.4	16.9
15	48.3	33.30	24.7	25.2
25	62.0	47.04	38.5	38.9