



# clamping module

## EV-20/180-5

Part number: 13293

FESTO



### Data sheet

Feature	Value
Stroke	5 mm
Clamping surface	20x180
Assembly position	Any
Mode of operation	single-acting
Operating pressure	2 ... 6 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Ambient temperature	-20 ... 40 °C
Product weight	270 g
Mounting type	with through hole
Pneumatic connection	M5
Materials note	Free of copper and PTFE
Material housing	Aluminium die cast
Material membrane	TPE-U(PU)