




FKV





Code-No.	Type	A	B	C	D	E	G	H	K	L	M	N	R	S	m [g]
122 500 050_..	FKV 25	25,3	6,5	30	45	45	75	57	62	52,5	75	10	46	M8x50	292
123 000 050_..	FKV 30	30,3	6,5	30	45	45	75	57	62	52,5	75	10	46	M8x50	273
123 500 050_..	FKV 35	35,4	8,5	40	60	60	100	76	75	70	100	10	57	M8x70	555
124 000 050_..	FKV 40	40,4	8,5	40	60	60	100	76	75	70	100	10	57	M8x70	530

R



Code-No.	Type	A	D	E	H	K	L	M	N	R	S	m [g]
122 000 070_..	R 20	20,1	45	45	-	62	45	-	-	46	M8x45	211
122 500 070_..	R 25	25,15	45	45	-	62	45	-	-	46	M8x45	210
123 000 070_..	R 30	30,15	45	45	-	62	45	-	-	46	M8x45	194
123 500 070_..	R 35	35,2	60	60	26	75	60	14	5,5	57	M8x60	376
124 000 070_..	R 40	40,2	60	60	26	75	60	14	5,5	57	M8x60	360

V



Code-No.	Type	A	D	E	H	K	L	M	N	R	S	m [g]
122 000 080_..	V 20	20,3	45	45	-	62	45	-	-	46	M8x45	202
122 500 080_..	V 25	25,3	45	45	-	62	45	-	-	46	M8x45	197
123 000 080_..	V 30	30,3	45	45	-	62	45	-	-	46	M8x45	187
123 500 080_..	V 35	35,4	60	60	26	75	60	14	5,5	57	M8x60	361
124 000 080_..	V 40	40,4	60	60	26	75	60	14	5,5	57	M8x60	334

Bestellhinweise siehe Seite 6-7 Order instructions see page 6-7