





KV





Code-No.	Type	A	B	C	D	E	G	H	K	L	M	R	S	m [g]
102 000 050_ _ _	KV 20	20,3	20,3	37,5	45	45	43,5	62	62	82,5	43,5	46	M8x45	385
102 500 050_ _ _	KV 25	25,2	25,2	37,5	45	45	43,5	62	62	82,5	43,5	46	M8x45	353
103 000 050_ _ _	KV 30	30,2	30,2	37,5	45	45	43,5	62	62	82,5	43,5	46	M8x45	321
103 500 050_ _ _	KV 35	35,3	35,3	50	60	60	60	75	75	110	60	57	M8x60	637
104 000 050_ _ _	KV 40	40,3	40,3	50	60	60	60	75	75	110	60	57	M8x60	584

KDVR



Code-No.	Type	A	B	C	D	E	G	H	K	L	P	R	S	T	m [g]
104 020 090_ _ _	KDVR 20-40	40,3	20,2	47	45	45	44,5	62	97,5	109,5	48	46	M8x35	M10x50	408
104 025 090_ _ _	KDVR 25-40	40,3	25,2	47	45	45	44,5	62	97,5	109,5	48	46	M8x35	M10x50	396
104 030 090_ _ _	KDVR 30-40	40,3	30,2	47	45	45	44,5	62	97,5	109,5	48	46	M8x35	M10x50	365

KDRR



Code-No.	Type	A	B	C	D	E	G	H	K	L	P	R	S	T	m [g]
102 040 110_ _ _	KDRR 20-40	40,3	20	47	45	45	44,5	62	97,5	109,5	48	46	M8x35	M10x50	452
102 540 110_ _ _	KDRR 25-40	40,3	25,1	47	45	45	44,5	62	97,5	109,5	48	46	M8x35	M10x50	442

Bestellhinweise siehe Seite 6-7 Order instructions see pages 6-7

