



**Fuse-link, low voltage, 4 A, AC 550 V, 80 kA, BS88/F1, 14 x 59 mm, gL/gG, BS**

**Part no. 4AMP 550V AC BS88 FUSE**  
**Catalog No. NSD4**

Similar to illustration

## Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	4
Rated voltage			AC 550 V
Construction size			BS88/F1
Size			14 x 59 mm
Utilization category			gL/gG
Breaking Capacity		kA	80
usable for size/applications			general industrial applications
Standard/Approval			BS
Shape			offset bladed tags
Standards/Regulations			BS88-2 IEC 60269-2
Optional accessories			fuse-holder 32NNS and SC32

## Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	4
Rated voltage		V	550
Voltage type			AC
Rated switching capacity		kA	80
Utilization category			gL/gG (cable protection/equipment protection)
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No