



8-32 UNC X .230 REF BINDING
 HEAD TERMINAL SCREW AND
 LOCKWASHER (SEMS) (4)




CIRCUIT DIAGRAM

NOTE -
 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON 2.125 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ----- 7 - 11 OZ
 RELEASE FORCE ----- 4 OZ MIN
 DIFFERENTIAL TRAVEL ---- .015 - .025
 OVERTRAVEL ----- .080 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
 SEE CIRCUIT DIAGRAM
 15A-120, 240, 480, OR 600 VAC
 1/2 HP-120 VAC; 1 HP-240 VAC
 0.8A-115 VDC; 0.4A-230 VDC
 PILOT DUTY 600 VAC MAX

B600



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/.04	X X
ONE PLACE	X,X	0.4/.016	X X X
TWO PLACES	X,XX	0.15/.006	X X X
THREE PLACES	X,XXX		X,XXX
ANGLES			

DESIGN UNITS

SI METRIC

US CUSTOMARY

WEIGHT

3MN19

M

DRAWING NUMBER

ISSUE

4

REPLACES

RELEASE NO. PR-11059

CHECK

REVISIONS

A	CO-51502	KAG	14 JUL 82
B	CO-53070	TSK	25 APR 83
C	CO-61338	GRT	26 MAY 87

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

FO-52848-A

DRAWN

D J S

12 APR 82

APR 82

APR 82

APR 82