

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430104](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E38085

**General**

Product Family [Wiring Devices](#)  
 Series [130143](#)  
 IP Rating N/A  
 NEMA Configuration NEMA 5-15  
 Overview [Heavy-Duty Industrial Wiring Devices](#)  
 Product Name Super-Safeway  
 Receptacle Type Single  
 Specialty N/A  
 Type Cordset  
 UPC 78678879554

**Physical**

Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 15.24m (50.0')  
 Locking Blade No  
 Poles 2-pole/3-wire

**Electrical**

Cord Type 16/3 SOOW  
 Current - Maximum per Contact 15.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 125V

**Material Info**

Engineering Number 1447B163



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130143](#) Series