




A23-7 □ □



**A** Actuator can't be take out.



**B** Actuator can be take out.



Panel Thickness:11.0mm Max.

**B**




Panel Thickness:16.0mm Max.

<b>Continuous Rating</b>	100 Amps 32VDC Max.
<b>Contact Resistance</b>	50MΩ Max
<b>Intermittent Rating</b>	150 Amps
<b>Cranking Rating</b>	500 Amps 5 sec.
<b>Insulation Resistance</b>	DC 500V 100MΩ Min
<b>Dielectric Strength</b>	AC 1000V 1 minute DC 2000V 1 minute
<b>Operation Temperature</b>	-30°C ~ +60°C
<b>Switch Function</b>	2P SPST OFF-ON

**FEATURES:**

- Material:  
Housing: Black, PA#66+33%GF, with white hot stamping  
Actuator: Red, PBT+15%GF  
Name Plate: White, ABS with black hot stamping  
Bottom: Black, PBT+15%GF  
Nut: Black, PA#66  
Hex Nut: Ni-plated, Brass

Внимание! Описание товара носит информационный характер и может отличаться от описания, представленного в технической документации производителя. Убедительно просим Вас при покупке проверять наличие желаемых функций и характеристик.



Сеть магазинов  
**КВАРЦ**  
Радиодетали и электронные компоненты

107023, Москва, ул. Буженинова, д. 16  
телефон: +7(495)963-6120  
факс: +7(495)963-4994  
e-mail: quartz1@quartz1.ru

111123, Москва, шоссе Энтузиастов, д. 31  
телефон: +7(495)788-8899 *многоканальный*  
e-mail: mgz@quartz1.ru  
http://www.quartz1.com