



R13-702








Rating	20A 14V DC, 10A 28V DC
Contact resistance	50mΩ Max
Insulation resistance	DC 500V 100MΩ Min
Dielectric strength	AC 1000V 1 minute
Cut out	
	0.7~3.0 mm max

FEATURES

- * **MATERIAL:** Frame is nylon. Terminals are plated brass.
- * **Position indicator:** The arrow icon can be optional either illuminated or non-illuminated. The position marks can be optional as (0, 1, 2, 3), (off, L, M, H) or other assigned symbols.
- * **LED** can be dependent or independent circuit.

R13-702 - - - -

FUNCTION	TERMINAL	LEGEND	LED COLOR
A 2P SPST OFF-ON	0 2  .187" SQ	N NONE	KNOB MARKING
B 3P SPDT OFF-ON-ON	KNOB	1  R13-702 20A14VDC	Optional legend on actuator, see page A1.
C 4P SP3T OFF-ON-ON-ON	1 	2  R13-702 10A28VDC	VOLTAGE
	FRAME COLOR	3  R13-702 20A14VDC 10A28VDC	1 12V DC
	KNOB COLOR	LIGHT CIRCUIT	2 24V DC
	LENS COLOR	N NONE	
		D LED dependent only for DC	
		I LED independent	