



## Heat Shrinkable Sleeving

### HIS-3 BAG

A 3:1 shrink ratio in handy 250mm lengths allows for both individual and large bundled wires to be sleeved quickly and easily.

#### Features and Benefits

- Comes in 5 colours: black, brown, grey, blue, green/yellow
- 3 sizes from 6mm to 40mm
- Ideal to carry in a toolbox
- General purpose electrical installation
- Colour identification
- Protection against mechanical abrasion and corrosion



HIS-3 BAG.

TYPE	Supplied ID mm	Recovered ID mm	Wall (WT) mm	Colour	Pack Cont.	Article No.
HIS-3-BAG-6/2MX	6	2	0.65	BK, BN, GY, BE, GNYE	15 x 250mm	308-30616
HIS3-BAG-12/4MX	12.4	4	0.80	BK, BN, GY, BE, GNYE	15 x 250mm	308-31216
HIS3-BAG-40/13MX	40	13	0.80	BK, BN, GY, BE, GNYE	15 x 250mm	308-34010



For more products see Section 2.1 in our Product Catalogue.

## Sleeving

### Glass Braided Sleeving

Helagain GSS is a range of lightweight, braided sleeving made from highly flexible glass fibre impregnated with silicone rubber. GSS has good resistance to chemical attack and has excellent flame resistance characteristics.

#### Features and Benefits

- Temperature range -60°C to +220°C
- Continuous (peak of +450°C)
- Intermittent temperature +290°C)
- Breakdown voltage: 1KV
- Colour: Cream/Off White – supplied in 25m coils



Glass braided sleeving.

TYPE	Bore dia mm	Colour	Pack Cont..
GSS1.0	1.0	White	25m
GSS1.5	1.5	White	25m
GSS2.0	2.0	White	25m
GSS2.5	2.5	White	25m
GSS3.0	3.0	White	25m
GSS4.0	4.0	White	25m
GSS5.0	5.0	White	25m
GSS6.0	6.0	White	25m
GSS7.0	7.0	White	25m
GSS8.0	8.0	White	25m
GSS10.0	10.0	White	25m