



-1. Wrenches

-1.1. ADJUSTABLE WRENCHES

- Standards: ISO 6787, DIN 3117 form, ASME B107.8M - 1996 and BS 6333
- High performance alloy steel
- Scale in mm for pre adjusting and accurate measurement
- Head combines slimness for accessibility with strength for performance
- Left-handed screw
- Black finish. Precision-hardened and anti-corrosion treated
- IP: Industrial pack

80 series

80

			A mm	B mm	C mm	D mm	
8069	7314150007028	5	110	13	4.0	9.0	60
8070	7314150007110	5	155	20	4.9	11.3	135
8071	7314150007202	5	205	27	6.0	12.9	255
8072	7314150007288	5	255	30	8.6	15.5	400
8073	7314150007363	5	305	34	11.9	18.0	665
8074	7314150007448	3	380	44	14.0	20.0	1035
8075	7314150007523	3	455	53	17.7	22.5	1665
8069 IP	7314150007042	50	110	13	4.0	9.0	60
8070 IP	7314150007134	40	155	20	4.9	11.3	135
8071 IP	7314150007226	50	205	27	6.0	12.9	255
8072 IP	7314150007301	30	255	30	8.6	15.5	400
8073 IP	7314150007387	20	305	34	11.9	18.0	665
8074 IP	7314150007462	20	380	44	14.0	20.0	1035
8075 IP	7314150007547	10	455	53	11.7	22.5	1665

