



PRODUCT-DETAILS

TY600-175

CABLE TIE 175LB 25IN NAT NYL X-HVY

General Information

Extended Product Type	TY600-175
Product ID	7TAG054360R0345
EAN	5415022140859
Catalog Description	CABLE TIE 175LB 25IN NAT NYL X-HVY
Long Description	Extra Heavy-Duty Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 631mm (24.84 Inches), Width of 9mm (0.35 Inches), Thickness of 1.8mm (0.07 Inches), Tensile Strength Rating of 778 Newtons (175 Pounds)

Ordering

EAN	5415022140859
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.034 lb 15.42 g
--------------------	--------------------

Container Information

Package Level 1 Units	50 piece
Package Level 1 Width	6 in

	152 mm
Package Level 1 Height	1.75 in 44 mm
Package Level 1 Depth / Length	29 in 737 mm
Package Level 2 Units	500 piece
Package Level 2 Width	8 in 203 mm
Package Level 2 Height	8 in 203 mm
Package Level 2 Depth / Length	26.5 in 673 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	7.2 in 182.88 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	Extra Heavy Duty
Standards	UL E49405
Tensile Strength	175 lb 780 N
Thickness	0.07 in 1.8 mm
UPC	786209513977

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY600-175
Instructions and Manuals	TY600-175

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties