



Powering Business Worldwide

pe.eaton.com

easy Programmable Relays

EASY200-POW

Dimensions:

- **Height:** 3.543 IN
- **Length:** 2.283 IN
- **Width:** 1.398 IN

Warranties:

- 1 year

Specifications:

- **Special Features:** Additional output voltage 12 Vdc at 20 mA, 85-264V maximum i/o
- **Type:** easy Power Supplies
- **Amperage Rating:** 0.25A at 24 Vdc
- **Frequency Rating:** 47-63 Hz
- **Quantity:** 1
- **Voltage Rating:** 100-240V
- **Connection:** 0.2-4.0mm² (solid), 0.2-2.5mm² (flexible), 22-12 AWG
- **Mounting:** Top-hat rail
- **Operating Temperature:** -25° to 55°C

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - EASY200-POW](#)

Certifications:

- EN 55022
- IEC 61000-4
- EN 60950
- IEC 60068-2-27
- EN 61000-4
- EN 55011

Product compliance: No Data



