



AMP Connect

MAIN MENU

HELP

Alphabetical
SEARCH

Picture
SEARCH

Part Number
SEARCH

Go To Step Search™ Screen


350713-1 -- 1 of 1 products

Soft Shell Connectors
Soft Shell - PCB Headers

General **INFO**

Sales **INFO**

Customer Drawings
SPECIFICATIONS



Line art represents typical product only.

 [PCB Layout](#)

Searchable Features:

Connector Line	Universal MATE-N-LOK
Mount Angle	Vertical
# of Circuits	12
Centerline	.250 x .250 [6.35 x 6.35] in. [mm]
Finish	Pre Tin
Contact Type	Pin
Lock Type	Positive Lock
Mount	PCB Thru Mount
Material	Phosphor Bronze
Contact Layout	Matrix
PCB Thickness	.062 [1.57] in. [mm]
Housing Material	Nylon
PCB Polarized	Non-Polarized
Solder Tail Length	.175 [4.45] in. [mm]

Other Properties:

Dim. A	1.050 [26.67] in. [mm]
Color	White
Housing Flammability Rating	UL 94V-0