

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0393570002](#)
Status: **Active**
Overview: Eurostyle Terminal Blocks
Description: 3.50mm Pitch Beau Eurostyle Fixed Mount PCB Terminal Block, 2 Circuits

Documents:

[3D Model \(PDF\)](#) [Drawing \(PDF\)](#)
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family Terminal Blocks
Series [39357](#)
Application N/A
Component Type One Piece
Overview [Eurostyle Terminal Blocks](#)
Product Name Eurostyle Fixed Mount
Taxonomy Terminal Blocks and Barrier St
Type Euro Block
UPC 756054634127

Physical

Circuits (Loaded) 2
Circuits (maximum) 2
Entry Angle Horizontal
Flammability 94V-0
Lock to Mating Part None
Net Weight 1.240/g
Number of Rows 1
Orientation Vertical
PC Tail Length 3.50mm
PCB Retention None
PCB Thickness - Recommended 1.60mm
Panel Mount No
Pitch - Mating Interface 3.50mm
Pitch - Termination Interface 3.50mm
Polarized to Mating Part No
Shrouded Fully
Stackable Yes
Surface Mount Compatible (SMC) No
Temperature Range - Operating -30° to +85°C
Wire Size AWG 16, 18, 20, 22, 24, 26, 28
Wire Size mm² 0.20-1.00

Electrical


Current - Maximum per Contact 17.5A
Voltage - Maximum 300V

Material Info

Engineering Number MX-MTB02008-0N

Reference - Drawing Numbers

Sales Drawing SD-39357-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[39357 Series](#)

This document was generated on 09/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION